

MIL-SPEC	Tyco Electronics	SEIP	GLENAIR COMMERCIAL	Wire Description	Solder Alloy
M83519/1-1	S0101R	H-M-1	077-01001	None	Sn63 Solder with ROL1 Flux
M83519/1-2	S0102R	H-M-2	077-01002	None	NO Thermal Indicator
M83519/1-3	S0103R	H-M-3	077-01003	None	
M83519/1-4	S0104R	H-M-4	077-01004	None	
M83519/1-5	S0105R	H-M-5	077-01005	None	
M83519/2-1	S0201R	H-ML-1	077-02001	M22759/32-20-90	Sn63 Solder with ROL1 Flux
M83519/2-2	S0202R	H-ML-2	077-02002	M22759/32-20-90	NO Thermal Indicator
M83519/2-3	S0203R	H-ML-3	077-02003	M22759/32-20-90	
M83519/2-4	S0204R	H-ML-4	077-02004	M22759/32-20-90	
M83519/2-5	S0205R	H-ML-5	077-02005	M22759/32-20-90	
M83519/2-6	S0206R	H-ML-6	077-02006	M22759/32-22-90	Sn63 Solder with ROL1 Flux
M83519/2-7	S0207R	H-ML-7	077-02007	M22759/32-22-90	NO Thermal Indicator
M83519/2-8	S0208R	H-ML-8	077-02008	M22759/32-22-90	
M83519/2-9	S0209R	H-ML-9	077-02009	M22759/32-22-90	
M83519/2-10	S0210R	H-ML-10	077-02010	M22759/32-22-90	
M83519/2-11	S0211R	H-ML-11	077-02011	M22759/32-24-90	Sn63 Solder with ROL1 Flux
M83519/2-12	S0212R	H-ML-12	077-02012	M22759/32-24-90	NO Thermal Indicator
M83519/2-13	S0213R	H-ML-13	077-02013	M22759/32-24-90	
M83519/2-14	S0214R	H-ML-14	077-02014	M22759/32-24-90	
M83519/2-15	S0215R	H-ML-15	077-02015	M22759/32-24-90	
M83519/2-16	S0216R	H-ML-16	077-02016	M22759/32-26-90	Sn63 Solder with ROL1 Flux
M83519/2-17	S0217R	H-ML-17	077-02017	M22759/32-26-90	NO Thermal Indicator
M83519/2-18	S0218R	H-ML-18	077-02018	M22759/32-26-90	
M83519/2-19	S0219R	H-ML-19	077-02019	M22759/32-26-90	
M83519/2-20	S0220R	H-ML-20	077-02020	M22759/32-26-90	
	Tyco Electronics	SEIP	GLENAIR	Braid Description	Solder Alloy
	S03-01-R	H-MB-106T	077-03001	Tin-Plated 640 CMA - 6" long	Sn63 Solder with ROL1 Flux
	S03-02-R	H-MB-206T	077-03002	Tin-Plated 640 CMA - 6" long	NO Thermal Indicator
	S03-03-R	H-MB-306T	077-03003	Tin-Plated 640 CMA - 6" long	
	S03-04-R	H-MB-406T	077-03004	Tin-Plated 640 CMA - 6" long	
	S03-05-R	H-MB-506T	077-03005	Tin-Plated 640 CMA - 6" long	

