



HIGH-AVAILABILITY AS22759 AND GLENAIR SIGNATURE WIRE

Available Stock • Fast Lead Times • No Order Minimums

M27500 Commercial Equivalents and Custom Solutions Available

AS22759 Slash Sheet	Glenair Commercial Part No.	Temperature Rating	Conductor	Plating	Conductor Code	Weight	Conductor AWG Range
SAE AS22759/16-19, ETFE							
M22759/16	GS22759-16*	150°C	Copper	Tin	TCC	Medium	24-00
M22759/17	GS22759-17	150°C	High-Strength Copper Alloy	Silver	SCA	Medium	26-20
M22759/18	GS22759-18	150°C	Copper	Tin	TCC	Light	26-10
M22759/19	GS22759-19	150°C	High-Strength Copper Alloy	Silver	SCA	Light	26-20
SAE AS22759/32-35, XL-ETFE							
M22759/32	GS22759-32	150°C	Copper	Tin	TCC	Light	30-12
M22759/33	GS22759-33	200°C	High-Strength Copper Alloy	Silver	SCA	Light	30-20
M22759/34	GS22759-34*	150°C	Copper	Tin	TCC	Normal (Dual Wall)	24-00
M22759/35	GS22759-35	200°C	High-Strength Copper Alloy	Silver	SCA	Normal (Dual Wall)	26-20
SAE AS22759/41-46, XL-ETFE							
M22759/41	GS22759-41*	200°C	Copper	Nickel	NCC	Normal (Dual Wall)	26-00
M22759/42	GS22759-42	200°C	High-Strength Copper Alloy	Nickel	NCA	Normal (Dual Wall)	26-20
M22759/43	GS22759-43*	200°C	Copper	Silver	SCC	Normal (Dual Wall)	26-00
M22759/44	GS22759-44	200°C	Copper	Silver	SCC	Light	26-12
M22759/45	GS22759-45	200°C	Copper	Nickel	NCC	Light	28-12
M22759/46	GS22759-46	200°C	High-Strength Copper Alloy	Nickel	NCA	Light	28-20

* GS maximum AWG = 8