



MIL-DTL-38999 Hermetic Connectors and Environmental Mates

B

Hermetic	Environmental	Hermetic	Environmental
230-003P09-35PN	D38999/26FA35SN	D38999/21YA98PN	D38999/26FA98SN
230-003P09-35PN	D38999/26FA35SN	D38999/21YB35XA	D38999/26FB35SA
230-003P15-97DN	D38999/26FD97PN	D38999/21YB5PN	D38999/26FB5SN
230-003P19-11DN	D38999/26FF11PN	D38999/21YB5PN	D38999/26FB5SN
231-100-H7Z113-35PN	MS27467E13F35S	D38999/21YB98PB	D38999/26FB98SB
231-100-H7Z113-35PN	MS27467E13F35S	D38999/21YB98PC	D38999/26FB98SC
231-100-H7Z113-35PN	MS27467E13F35S	D38999/21YB98PN	D38999/26FB98SN
231-100-H7Z113-35PN	MS27467E13F35S	D38999/21YB99PN	D38999/26FB99SN
231-100-H7Z113-35PN	MS27467E13F35S	D38999/21YC35PN	D38999/26FC35SN
231-100-H7Z113-35PN	MS27467E13F35S	D38999/21YC4PN	D38999/26FC4SN
231-100-H7Z113-35PN	MS27467E13F35S	D38999/21YC4PN	D38999/26FC4SN
231-100-H7Z115-35PA	MS27467E15F35SA	D38999/21YC4PN	D38999/26FC4SN
231-100-H7Z115-35PA	MS27467E15F35SA	D38999/21YC4SN	D38999/26FC4PN
231-100-H7Z115-35PA	MS27467E15F35SA	D38999/21YC4SN	D38999/26FC4PN
231-100-H7Z115-35PA	MS27467E15F35SA	D38999/21YC4SN	D38999/26FC4PN
231-100-H7Z115-35PA	MS27467E15F35SA	D38999/21YC98PA	D38999/26FC98SA
231-100-H7Z115-35PA	MS27467E15F35SA	D38999/21YC98PA	D38999/26FC98SA
231-100-H7Z115-35PA	MS27467E15F35SA	D38999/21YC98PA	D38999/26FC98SA
231-100-H7Z115-35PA	MS27467E15F35SA	D38999/21YC98PA	D38999/26FC98SA
231-100-H7Z117-35PN	MS27467E17F35S	D38999/21YD5PN	D38999/26FD5SN
231-100-H7Z117-35PN	MS27467E17F35S	D38999/21YD97PA	D38999/26FD97SA
231-100-H7Z117-35PN	MS27467E17F35S	D38999/21YD97PA	D38999/26FD97SA
231-100-H7Z117-35PN	MS27467E17F35S	D38999/21YD97PN	D38999/26FD97SN
231-100-H7Z117-35PN	MS27467E17F35S	D38999/21YE6XN	D38999/26FE6SN
231-100-H7Z117-35PN	MS27467E17F35S	D38999/21YG16PN	D38999/26FG16SN
231-100-H7ZL17-35PN	MS27467E17F35S	D38999/21YG39PN	D38999/26FG39SN
232-100-H5Z110-35PN	MS27473E10F35S	D38999/23NA35PN	D38999/26FA35SN
233-100-H7ZL17-06DN	D38999/26FE6PN	D38999/23NB5SN	D38999/26FB5PN
233-100-H7ZL17-06DN	D38999/26FE6PN	D38999/23ND35PA	D38999/26FD35SA
D38999/21NA35PN	D38999/26FA35SN	D38999/23ND97DN	D38999/26FD97PN
D38999/21NA35PN	D38999/26FA35SN	D38999/23NF11DN	D38999/26FF11PN
D38999/21NB35PN	D38999/26FB35SN	D38999/23NG16PN	D38999/26FG16SN
D38999/21ND35PA	D38999/26FD35SA	D38999/23NG16PN	D38999/26FG16SN
D38999/21NJ19PN	D38999/26FJ19SN	D38999/23YA35PN	D38999/26FA35SN
D38999/21NJ19PN	D38999/26FJ19SN	D38999/23YA35PN	D38999/26FA35SN
D38999/21NJ35DA	D38999/26FJ35PA	D38999/23YA35PN	D38999/26FA35SN
D38999/21NJ35DA	D38999/26FJ35PA	D38999/23YB35CN	D38999/26FB35SN
D38999/21NJ35DB	D38999/26FJ35PB	D38999/23YB35PA	D38999/26FB35SA
D38999/21NJ35DB	D38999/26FJ35PB	D38999/23YB35PN	D38999/26FB35SN
D38999/21NJ35DC	D38999/26FJ35DC	D38999/23YB35PN	D38999/26FB35SN
D38999/21NJ35DC	D38999/26FJ35DC	D38999/23YB35PN	D38999/26FB35SN
D38999/21YA98PN	D38999/26FA98SN	D38999/23YB35SN	D38999/26FB35PN

Dimensions in Inches (millimeters) are subject to change without notice.

MIL-DTL-38999 Hermetic Connectors and Environmental Mates



Hermetic	Environmental
D38999/23YB35SN	D38999/26FB35PN
D38999/23YB35SN	D38999/26FB35PN
D38999/23YB98PN	D38999/26FB98SN
D38999/23YC35PC	D38999/26FC35SC
D38999/23YC35PN	D38999/26FC35SN
D38999/23YC35SB	D38999/26FC35PB
D38999/23YC35SB	D38999/26FC35PB
D38999/23YC35SB	D38999/26FC35PB
D38999/23YC35SN	D38999/26FC35PN
D38999/23YC35SN	D38999/26FC35PN
D38999/23YC4PN	D38999/26FC4SN
D38999/23YC98PN	D38999/26FC98SN
D38999/23YC98PN	D38999/26FC98SN
D38999/23YC98PN	D38999/26FC98SN
D38999/23YC98PN	D38999/26FC98SN
D38999/23YE26SA	D38999/26FE26PA
D38999/23YE6SN	D38999/26FE6PN
D38999/23YG41CN	D38999/26FG41SN
D38999/23YH35CN	D38999/26FH35SN
D38999/23YH35PA	D38999/26FH35SA
D38999/23YH35PA	D38999/26FH35SA
D38999/23YJ29SN	D38999/26FJ29PN
D38999/23YJ29SN	D38999/26FJ29PN
D38999/25YH35PN	D38999/26FH35SN
D38999/48YC35PN	D38999/46FC35SN
MS27469Y23N35C	MS27467E23F35S
MS27470Y11D35S	MS27467E11F35P
MS27470Y15E35PA	MS27467E15F35SA
MS27470Y23D21P	MS27467E23F21S
MS27471Y11E35P	MS27467E11F35S
MS27471Y11E35P	MS27467E11F35S
MS27471Y13D98PB	MS27467E13F98SB
MS27475Y10E35P	MS27473E10F35S
MS27477Y14E18PB	MS27473E14F18SB
MS27477Y14N18S	MS27473E14F18P
MS27478Y10E35P	MS27473E10F35S
MS27478Y10N35C	MS27473E10F35S
MS27478Y10N35C	MS27473E10F35S
MS27478Y18N35P	MS27473E18F35S

Dimensions in Inches (millimeters) are subject to change without notice.