

Contact arrangements

SHELL SIZE / CONTACT ARRANGEMENTS (FACE OF PIN INSERT)					
<b>16-A1</b> 1X #8	<b>16-1</b> 1X #4	<b>20-A1</b> 1X #2	<b>20-1</b> 1X #1/0	<b>22-1</b> 1X #2/0 [consult factory]	<b>22-2</b> 2X #8
<b>22-3</b> 3X #8	<b>24-1</b> 1X #4/0 [consult factory]	<b>24-2</b> 2X #4	<b>24-4</b> 4X #8	<b>28-2</b> 2X #2	<b>28-3</b> 3X #2
<b>28-4</b> 4X #4	<b>28-6</b> 6X #8	<b>32-2</b> 2X #1/0	<b>32-3</b> 3X #1/0	<b>32-4</b> 4X #2	
			<p>#8 #4 #2 #1/0 #2/0 #4/0</p> <p>Contact Size Key</p>		
<b>36-2</b> 2X #2/0 [consult factory]	<b>36-4</b> 4X #1/0	<b>40-3</b> 3X #2/0 [consult factory]			

PLUG POLARIZATION POSITIONS				
Position	A°	B°	C°	D°
<b>1</b>	76	148	212	284
<b>2</b>	135	170	200	310
<b>3</b>	49	169	200	244
<b>4</b>	66	140	200	257
<b>5</b>	62	145	180	280
<b>6</b>	79	153	197	272

RECEPTACLE POLARIZATION POSITIONS				
Position	A°	B°	C°	D°
<b>1</b>	76	148	212	284
<b>2</b>	135	170	200	310
<b>3</b>	49	169	200	244
<b>4</b>	66	140	200	257
<b>5</b>	62	145	180	280
<b>6</b>	79	153	197	272