




SERIES 79

MICROCRIMP®

Micro-Crimp

- Crimp, PCB, fiber optic, coax, power and pitot
- Precision machined aluminum shells sealed to IP67
- High-density #23 contact arrangements set on .076 centers
- Blind mating for rack and panel applications
- Environmental, hermetic and filter versions
- Integrated ground spring for improved EMI shielding

The ultraminiature crimp contact rectangular with advanced environmental and EMC performance



SERIES 79 Micro-Crimp

High-reliability crimp contact performance

MICROCRIMP®

SERIES 79 MICRO-CRIMP PRODUCT SELECTION GUIDE



Crimp Terminated Cable Connectors



Crimp Terminated Panel Mount Connectors



Straight PCB Panel Mount and Free-Standing Connectors




Right Angle PCB Panel Mount and Free-Standing Connectors




Backshells and Accessories, EMI Adapters and Protective Covers

Blind Mate Guide Pins and Sockets



Guide Pins
Connector may be supplied with stainless steel non-removable guide pins.



Guide Sockets
Connector may be supplied with stainless steel non-removable bushings.

Selected Contact Types



Shell Size	Contact Arrangement	Contact Quantity		
		#23	#16	#12
A	A-5	5	—	—
B	B-2P2	—	2	—
	B-9	9	—	—
C	C-13	13	—	—
D	D-15	15	—	—
	D-3P3	—	3	—
	D-7P2	5	2	—
E	E-11P2	9	2	—
	E-19	19	—	—
	E-7P3	4	3	—

Shell Size	Contact Arrangement	Contact Quantity		
		#23	#16	#12
F	F-15P2	13	2	—
	F-23	23	—	—
	F-5P5	—	5	—
G	G-33	33	—	—
H	H-10P4	6	—	4
	H-29P7	22	7	—
	H-36P2	34	—	2
	H-54P2	52	2	—
I	I-5P5	—	—	5
	I-66	66	—	—

Shell Size	Contact Arrangement	Contact Quantity		
		#23	#16	#12
J	J-17P4	13	4	—
	J-25P2	23	2	—
	J-33	33	—	—
	J-7P7	—	7	—
K	K-27P4	23	4	—
	K-35P2	33	2	—
	K-43	43	—	—
	K-9P9	—	9	—
L	L-6P6	—	—	6
M	M-78	78	—	—
	M-102	102	—	—

Performance Specifications

Current rating	Contact size #23 5 Amps, size #16 13 Amps, size #12 23 Amps maximum
Voltage rating (DWV)	Contact size #23 500 VAC rms. size #16 and #12 1800 VAC rms. Sea level.
Insulation resistance	5000 megohms minimum
Operating temperature	-65° C. to +150° C.
Contact resistance	5 milliohms maximum
Water ingress protection	IP67
Shielding effectiveness	>75 dB attenuation from 100 MHz to 1000MHz, >60dB 1GHz to 4GHz, >40dB 4GHz to 10GHz.



For more information contact Glenair at 818-247-6000 or visit our website at www.glenair.com U.S. CAGE code 06324