

	<b>240-515J</b>	<b>Jam Nut Receptacles MS3454</b>	<b>Page B-100</b>
	<b>240-515W</b>	<b>Wall Mount Receptacles MS3450</b>	<b>Page B-102</b>
	<b>240-515A</b>	<b>Connector Adapters</b>	<b>Page B-104</b>

**Notes**

1. Materials/Finishes: Shells, Jam Nut, Coupling Nut - See Table II  
Insulators - high grade rigid dielectric/N.A.  
Seals - Fluorosilicone  
Contacts: Copper alloy 50 $\mu$ " Gold over 50 $\mu$ " Nickel
2. Assembly to be identified with Glenair's name, part number, and date code - space permitting.
3. Insert Arrangement in accordance with MIL-STD-1651. (Arrangement shown for reference only)
4. EMI Circular Filter receptacle connectors designed to meet requirements of MIL-DTL-5015 Series III.
5. All contacts to have identical filter value. Other filter arrangements available, contact factory.
6. Electrical Ratings: DWV- 500 VDC; Standard Operating Voltage 200 VDC.
7. Insulation Resistance: 5000 MegOhms Min. at 200 VDC for classes A, B, C, and H.  
1,000 MegOhms Min. at 100 VDC for classes X, Y, and Z
8. Operating Temperature -55°C to +125°C (Env Class Connectors)
9. Other filter styles (Pi, C-L, L-C, Unbalanced Pi, Multi-Stage, Multi-Value) are available, please consult the factory.

Dimensions in inches (millimeters) and are subject to change without notice.