


## Recommended Panel Cutout Dimensions for Panel Mount Connectors



PANEL-MOUNT CUT-OUT DIMENSIONS

GHSM Panel Cutouts						
Layout	A	B	C	D	E	F
	± .003 (0.08)	± .002 (.05)	± .002 (0.05)	± .002 (0.05)	+ .005 (0.13) - .000 (-0.00)	± .002 (0.05)
9	.565 (14.35)	.410 (10.41)	.091 (2.31)	.347 (8.81)	.256 (6.50)	.126 (3.20)
15	.715 (18.16)	.560 (14.22)	.091 (2.31)	.347 (8.81)	.256 (6.50)	.126 (3.20)
21	.865 (21.97)	.710 (18.03)	.091 (2.31)	.347 (8.81)	.256 (6.50)	.126 (3.20)
25	.965 (24.51)	.810 (20.57)	.091 (2.31)	.347 (8.81)	.256 (6.50)	.126 (3.20)
31	1.115 (28.32)	.960 (24.38)	.091 (2.31)	.347 (8.81)	.256 (6.50)	.126 (3.20)
37	1.265 (32.13)	1.110 (28.19)	.091 (2.31)	.347 (8.81)	.256 (6.50)	.126 (3.20)
51-2	1.615 (41.02)	1.460 (37.08)	.091 (2.31)	.347 (8.81)	.256 (6.50)	.126 (3.20)
67	2.015 (51.18)	1.858 (47.19)	.091 (2.31)	.347 (8.81)	.256 (6.50)	.126 (3.20)

### Flange to Flange Mated Dimensions

