




10K PSI / 700 BAR / 7000M
**SuperG55™ High-Pressure,
 Dry-Mate Subsea Connectors**



Key mechanical and environmental features

**SUPERG55™ PRESSURE-BALANCED OIL-FILLED CABLE
 CONNECTOR PLUG (CCP)**




SuperG55™ Performance Specifications	
Mating Cycles	500
Pressure	689 Bar (10,000 PSI) Mated and Un-mated
Operating Temperature	-20°C to +90°C
Voltage Rating	600 VDC / 440 VAC
Current (max.)	5 to 18 Amps (dependant on contact and cable conductor sizes)

SuperG55™ Material/Finish	
Shells	316L Stainless Steel/ Passivated
Insulator	PEEK/NA
Insert	Neoprene/NA
Contacts	Copper Alloy/Gold Plated
O-rings	Nitrile/NA
Overmold and Cable	Polyurethane or Neoprene/NA
Coupling Nut	316L Stainless Steel/ Protective Coating Blue
Bulkhead Receptacle Tails	PTFE Insulated 16 AWG Wire/NA
Cable	Polyurethane or Neoprene Jacketed/NA

Bulkhead Mounting Torque	Size 15 - 14.12NM (125LB.INS.) Size 20 - 18.64NM (165LB.INS.) Size 24 - 25.42NM (225LB.INS.)
--------------------------	--

SUPERG55™ FLANGE CONNECTOR RECEPTACLE (FCR)



NON-STANDARD MATERIALS: Other material options are available as part of our non-catalog offerings including Anodized aluminium, Titanium, and Aluminium Bronze. Glenair is also able to supply SuperG55™ interconnects in composite thermoplastic (PEEK) to meet application requirements for reduced cathodic corrosion as well as weight reduction without affecting connector performance.

HIGH-SPEED ETHERNET: The SuperG55™ Ethernet option is available in the 1508, 2013 and 2021 contact configurations and provides both high speed (Up to 1GB) and power (600Volts) in a full subsea environment (10,000PSI). Gigabit speed data transfer up to a distance of 75mtrs.

SUBSEA/ DEEPWATER: SUPERG55™

